

**Part No:** 801-619CF

**Fabricated Fittings**

**Tees**

**Desc:** 10X1-1/4 CPVC RED TEE SOC SCH80 FAB

**MSRP:** 1331.53

**Part Code:** 097

**Weight(lbs):** 23.056

**Weight(kg):** 10.458

**Weight(gm):** 10458

**Size:** 10


**Color:** GRAY

**Material:** CPVC

**Schedule** Schedule 80

**Connection** Socket X Socket X Socket

**Type** Reduction



|                   |                     |                    |                      |               |
|-------------------|---------------------|--------------------|----------------------|---------------|
| <b>G</b> = 4-1/4  | <b>M</b> = 11-15/16 | <b>M1</b> = 2-1/16 | <b>M2</b> = 11-15/16 | <b>G1</b> = 7 |
| <b>G2</b> = 4-1/4 | <b>H</b> = 9-1/2    | <b>H1</b> = 8-9/16 | <b>H2</b> = 9-1/2    | <b>L</b> = 19 |

## Fabricated Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/4 & larger ± 1/2 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows, tees, crosses; ± 1/4 inch.; wyes ± 1/2 inch; 14" & larger inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/4 inch; 14" & larger ± 1/2 inch.

**L** = Overall length of fittings; ± 1/2 inch; wyes ± 1 inch; 14" & larger ± 1 inch.

**M** = Outside diameter of socket/thread hub; ± 1/4 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/2 inch.

**W** = Height of cap; ± 1/4 inch.

## Typical Fabricated Dimension References

