

**Part No:** 835-003SR

**Schedule 80 PVC & CPVC Adapter**
**Desc:** 3/8 PVC FEMALE ADAPTER SOCXSRFPT SCH80

**MSRP:** 9.38


**Weight(lbs):** 0.035

**Weight(kg):** 0.016

**Weight(gm):** 16

**Size:** 3/8"

**Color:** GRAY

**Material:** PVC

**Connection** Socket x SR Fipt

**Type** Standard

### Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

### Typical Molded Dimension References

