

Part No: 835-098SR

Schedule 80 PVC & CPVC Adapter
Desc: 3/4X1/4 PVC FEMALE ADPT SOCXSRFPT SCH80

MSRP: 23.6

Part Code: 086


Weight(lbs): 0.066

Weight(kg): 0.03

Weight(gm): 30

Size: 3/4 X 1/4

Color: GRAY

Material: PVC

L = 1-31/32

M = 1-13/32

M1 = 27/32

N = 11/32

Connection Socket x SR Fipt

Type Reduction

Injection Molded Dimension References:

G = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; $\pm 1/32$ inch.

H = Intersection of center lines to face of fitting; 90° elbows tees, crosses; $\pm 1/32$ inch.

J = Intersection of center lines to bottom of socket/thread; 45° elbows; $\pm 1/32$ inch

L = Overall length of fittings; $\pm 1/16$ inch.

M = Outside diameter of socket/thread hub; $\pm 1/16$ inch.

N = Socket bottom to socket bottom; couplings; $\pm 1/16$ inch.

W = Height of cap; $\pm 1/16$ inch

Typical Molded Dimension References

