

**Part No:** 875-578

**Schedule 80 PVC & CPVC**

**Wye**

**Desc:** 8X2 PVC WYE SOC SCH80 (BUSHED) 100PSI

**MSRP:** 2432.98

**Part Code:** 080

**Weight(lbs):** 15.45

**Weight(kg):** 7.008

**Weight(gm):** 7008


**Size:** 8"X8"X2"

**Color:** GRAY

**Material:** PVC

**Connection** Socket x Socket x Socket

**Type** Reduction



**G** = 15/32

**G1** = 10-3/16

**G2** = 8-1/4

**H** = 3-17/32

**H1** = 11-23/32

**H2** = 12-1/4

**L** = 15-3/4

**M** = 9-23/32

**M1** = 9-23/32

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses;  $\pm 1/32$  inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses;  $\pm 1/32$  inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows;  $\pm 1/32$  inch

**L** = Overall length of fittings;  $\pm 1/16$  inch.

**M** = Outside diameter of socket/thread hub;  $\pm 1/16$  inch.

**N** = Socket bottom to socket bottom; couplings;  $\pm 1/16$  inch.

**W** = Height of cap;  $\pm 1/16$  inch

## Typical Bushing Dimension References

