

Part No: 95032J100-015

All

AV-1

Desc: 1-1/2 DIAPHRAGM VALVE CPVC FLG FKM WITH 80PSI AIR TO SPRING CLOSE LINEAR ACTUATOR WITH INDICATOR

MSRP: 3231.62

Part Code: 552

Weight(lbs): 5.128

Weight(kg): 2.326

Weight(gm): 2326

Size:

Color:

Material:

Connection FKM O-ring and FKM Diaphragm Flanged


Under

Development

Injection Molded Dimension References:

- G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.
- H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.
- J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch
- L** = Overall length of fittings; ± 1/16 inch.
- M** = Outside diameter of socket/thread hub; ± 1/16 inch.
- N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.
- W** = Height of cap; ± 1/16 inch

Typical Molded Dimension References



The information printed here is based on current information & product design at the time of publication and is subject to change without notification. Spears® ongoing commitment to product improvement may result in some variation. No representation, guarantees or warranties of any kind are as to its accuracy, suitability for particular application or results to be obtained therefrom. For verification of technical data or additional information, please contact Spears® Technical Service Department :: WEST COAST : (818) 364-1611 - EAST COAST : (717) 938-9006