

**Part No:** S1720C05F

**Valves**

**Swing & Spring Check**

**Desc:** 1/2 PVC CL TU UTILITY SW CK VLV THD EPDM

**MSRP:** 41.26

**Part Code:** 026

**Weight(lbs):** 0.337

**Weight(kg):** 0.153

**Weight(gm):** 153

**Size:** 1/2"

**Color:** CLEAR


**Material:** PVC

**Type** Utility Swing Check

**Connection** Fipt (TU)

**Body Color** Clear

**Pressure Rating** 150 psi @ 73° F Full Flow (Open)  
75 psi Back Pressure (Closed)



**A** = 1-15/16

**B** = 3-23/32

**C** = 5

**D** = 2- 1/8

## Injection Molded Dimension References:

**G** = (LAYING LENGTH) intersection of center lines to bottom of socket/thread; 90° elbows, tees, crosses; ± 1/32 inch.

**H** = Intersection of center lines to face of fitting; 90° elbows tees, crosses; ± 1/32 inch.

**J** = Intersection of center lines to bottom of socket/thread; 45° elbows; ± 1/32 inch

**L** = Overall length of fittings; ± 1/16 inch.

**M** = Outside diameter of socket/thread hub; ± 1/16 inch.

**N** = Socket bottom to socket bottom; couplings; ± 1/16 inch.

**W** = Height of cap; ± 1/16 inch

## Typical Molded Dimension References

