

Enclosures **J Series**

## Fiberglass TeleControl Enclosure 14 x 7 x 6 Inches J Series with Hinged, Latched Opaque Cover



**Catalog  
Number**

J1407TC

**UPC**

785928904660


### DESCRIPTION

14H x 7W x 6D Inches TeleControl Series Fiberglass with Hinged, Latched Opaque Cover is designed to house telephones. Features a modest overhang raised cover on a flange mounted base. Accommodates standard back panel mounting to secure the phone.

### APPLICATION

- Designed to house telephones
- Industrial enclosure for harsh; aggressive environments
- Designed for general electrical and electronic applications; and any application that has associated environmental concerns
- Can be configured with cutouts; windows; and modifications that make the finished product truly unique
- Enhance any instrument installation and accommodate standard back-panel mounting

### FEATURES



- Increased wall thickness vs. competitive models offers structural support and prevents potential water ingress
- Integral mounting flange vs. mounting feet (no assembly required)
- Molded-in inserts provide added pull-out strength
- Opaque Cover
- Overhang cover on smooth sided base
- High temperature; flame retardant; non-corrosive
- All stainless hardware latches and screws
- Full-length; stainless-steel hinge
- Chemically resistant; fiberglass reinforced polyester
- Non-corrosive; environmental designs
- Stainless steel retention chain on screw covers
- Continuous polyurethane gasket
- Manufactured with SolarGuard®, Stahlin's proprietary formulation of non-halogenated fiberglass, offering superior resistance to outdoor exposure, chemicals and flames.
- Back Panels Available for all sizes

## General Information

|                               |                                                |
|-------------------------------|------------------------------------------------|
| Color                         | Gray                                           |
| Cover Type                    | Opaque                                         |
| Mounting Type                 | Wall Mount                                     |
| Material                      | Fiberglass                                     |
| Back Panel Screw Size         | #10-32 x 3/8                                   |
| Back Panel Recommended Torque | 16-20 in-lbs                                   |
| Back Panel Screw Material     | 304 SS                                         |
| Installation Mounting Torque  | 45 in-lbs Max                                  |
| Metal Inserts                 | Brass                                          |
| Hinge Material                | 304 SS                                         |
| Latch Material                | 304 SS                                         |
| Gasket Material               | Poured In Place (PIP)<br>Polyurethane Seamless |
| Country of Origin             | USA                                            |

## DIMENSIONS

|                   |         |
|-------------------|---------|
| Height (in)       | 15.87   |
| Width (in)        | 8.75    |
| Depth (in)        | 6.81    |
| Height (mm)       | 403.098 |
| Width (mm)        | 222.25  |
| Depth (mm)        | 172.974 |
| Usable Depth (in) | 6       |
| Usable Depth (mm) | 152     |

## STANDARDS

|                                   |                           |
|-----------------------------------|---------------------------|
| NEMA 10250; UL 50; UL 50e; UL508A | cULus Listed File #E64358 |
| CSA Std. C22.2                    | cULus Listed File #E64358 |
| Type                              | 1; 3R; 4; 4X; 6P; 12      |
| IEC 60529; UL Listed #E362920     | IP66                      |
| Plenum Space UL2043               | Compliant                 |
| Temperature Range °F              | -76°F to +274°F           |
| Temperature Range °C              | -60°C to +134°C           |
| IEC 62262 Impact Rating Listed    | IK10 per File #E362920    |
| Flammability Rating               | UL94-5VA                  |
| NFPA No. 101 Flame Spread         | Class A(1)                |
| Outdoor Exposure UL746c           | (f1) Rated                |
| CE                                | Certified                 |