






810007

Preset Torque Screwdriver - PM Series, 1 - 5 in-lb

PRODUCT DETAILS

- Bi-directional accuracy of +/- 6% preset value
- Meets or exceeds ASME B107.300-2010 and ISO 6789
- Operator cannot over-torque, clutch releases automatically when desired torque has been achieved
- Short dwell designed to prevent repetitive motion injuries
- Preset torque using torque tester and insert a bit to use
- Can be set in any unit of torque measurement
- Long shaft for use in limited-access applications
- Uses standard 1/4" bits, adapters, and sockets
- Polished aluminum exterior
- Anti-backlash design enhances repeatability
- Can be ordered preset from factory with calibration certificate from our ISO/IEC 17025 Accredited Calibration Laboratory

PRODUCT ATTRIBUTES

Product	MODEL	 lbf·in	 L	 lb
810007	PM 5	1-5 lbf·in	5.5 in	0.25 lb