








810-ATS-NM
Adjustable Torque Screwdriver, Nm



PRODUCT DETAILS

- Bi-directional Accuracy of +/- 6% Indicated Value from 20% to 100% of capacity
- Meets or exceeds ASME B107.300-2010 and ISO 6789
- Operator cannot over-torque, clutch releases automatically when desired torque has been achieved
- Scale on the shaft is marked in dual incrementation (in lb and Nm) on Cal 36/4, kgf•cm on CAL 40
- Magnifying lens improves the view of a clearly engraved scale
- To operate, simply dial torque setting and insert bit
- Anti-backlash design enhances repeatability
- Comes with FREE calibration certificate from our ISO/IEC 17025 Accredited Calibration Laboratory

PRODUCT ATTRIBUTES

| Product | MODEL |  N·m |  Nm |  |  |  |
|---------------|---------------|---|---|---|---|---|
| 810017 | CAL 36/4 EURO | 0.2-4.06 N·m | 0.2 N·m | 1/4 in | 7.8 in | 0.5 lb |