



## Electric Drum Control Switches

Single Speed Reversing Drum Controls for 1 and 3 phase motors up to 7.5 hp

- **UL and CSA Recognized** components throughout.
- **Enclosures** to suit your application needs. NEMA 1 (industrial) rated switches provide protection against dirt and corrosion for most indoor applications. NEMA 4 (watertight) rated switches keep dirt and water out, and are approved for most outdoor applications.
- **Wiring Diagram** is supplied inside the enclosure for convenient reference.
- **Two-Year Limited Warranty**

**WHEN ORDERING PLEASE INCLUDE THE FOLLOWING:** voltage and phase required, and motor horsepower.

Drum control switches for 115 volt single phase motors up to 1.5 hp, include 8 ft power cord with grounded plug.

### Electric Drum Control Switches – Horsepower Ratings – Section 2

model number	description	Voltage/Phase/Hertz with maximum rated motor hp				approx. ship wt.
		115/1/60 <sup>1</sup>	230/1/60	230/3/60	460/3/60	
10L2A1	NEMA 1	to 1.5 hp	to 2 hp	to 3 hp	to 3 hp	3 lb
10L7E1	NEMA 1	to 1.5 hp	to 3 hp	to 5 hp	to 7.5 hp	3 lb
10L2A4	NEMA 4 – watertight	to 1.5 hp	to 2 hp	to 3 hp	to 3 hp	7 lb
10L7E4	NEMA 4 – watertight	to 1.5 hp	to 3 hp	to 5 hp	to 7.5 hp	7 lb

Please contact factory or nearest Thern Distributor for firm fixed price and delivery.

<sup>1</sup> Controls for 115 volt single phase motors up to 1.5 hp, include 8 foot power cord with grounded plug.

#### Important:

It is the owner's or operator's responsibility to determine the suitability of the equipment to its intended use. Study all applicable codes, manuals, and regulations. Be sure to read the Owner's Manual supplied with the equipment before operating it.