



Actual

**Catalog Number:** 5345SST6  
**Product ID:** 7TAD012420R0133  
**UPC Number:** 78621008048  
**EAN Number:** 05415022450200  
**Status:** A

1-1/4 Inch Liquidtight Fitting for Flexible Metallic Conduit, 45 Degree, UL/CSA Listed, High UV Resistance, NEMA Ratings: 3, 3R, 4, 4X, Length 3.90 Inches/99.06mm, Width 2.25 Inches/57.15mm, Height 2.86 Inches/72.64mm, Temperature Range 0 to 105 Degrees C, 316 Stainless Steel with Duraplated Ground Cone

Corrosive environments can cause traditional metallic fittings to corrode and require replacement. The new stainless steel T&B Liquidtight Fittings are constructed of type 316 stainless steel to resist corrosion, all while offering high strength, UV resistance, and extreme performance up to 105 Degrees Celsius.

- NEMA Ratings: 3, 3R, 4, 4X
- CSA and UL Listed
- Ideal for Food and Beverage, Pharmaceutical, Petrochemical, Wastewater Processing, Salt Water and Other Corrosive Environments

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Type	45 Degree Fitting for Flexible Metallic Conduit
Special Features	Stronger and More UV-resistant than Nonmetallic Fittings
Application	Connects Flexible Metallic Liquidtight Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	316 Stainless Steel with Duraplated Ground Cone
Finish	None
Color	Metallic
NEMA Rating	3, 3R, 4, 4X
Insulation	Y
Temperature Rating	105 C

#### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel
Surface protection	Untreated
Total length	99.06mm
Total height	72.64mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	Y
	Y



Approved in combination with protective  
conduit UL

Approved in combination with protective N  
conduit FI

Operating temperature 0-105°C

### Packaging

Inner Quantity 5

Inner Dimensions (inches) 9.5x6.5x4.5

Outer Quantity 25

Outer Dimensions (inches) 23.31x6.81x9.81

Weight Uom 1.01 lbs. Each

### Documents / Support Tools

3D Rendering Available on Website

Technical Drawing / Data Sheet TDS000126

Instruction Sheet TA05037-TB2

Support/Tools Available on Website

Marketing Brochure US Available on Website

Catalog US Available on Website