



Actual

**Project:** JBS MOPAC  
**Location:** SOUTERDON  
**YALE**

**Catalog Number:** 5355SST6  
**Product ID:** 7TAD012420R0137  
**UPC Number:** 78621008089  
**EAN Number:** 05415022450484  
**Status:** Active

1-1/4 Inch Liquidtight Fitting for Flexible Metallic Conduit, 90 Degree, UL/CSA Listed, High UV Resistance, NEMA Ratings: 3, 3R, 4, 4X, Length 4.06 Inches/103.12mm, Width 2.25 Inches/57.15mm, Height 3.48 Inches/88.39mm, Temperature Range 0 to 105 Degrees C, 316 Stainless Steel with Duraplated Ground Cone

Corrosive environments can cause traditional metallic fittings to corrode and require replacement. The new stainless steel T&B Liquidtight Fittings are constructed of type 316 stainless steel to resist corrosion, all while offering high strength, UV resistance, and extreme performance up to 105 Degrees Celsius.

- NEMA Ratings: 3, 3R, 4, 4X
- CSA and UL Listed
- Ideal for Food and Beverage, Pharmaceutical, Petrochemical, Wastewater Processing, Salt Water and Other Corrosive Environments

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B Industrial Fitting
Type	90 Degree Fitting for Flexible Metallic Conduit
Special Features	Stronger and More UV-resistant than Nonmetallic Fittings
Application	Connects Flexible Metallic Liquidtight Conduit to a Box or Enclosure
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	316 Stainless Steel with Duraplated Ground Cone
Finish	None
Color	Metallic
NEMA Rating	3, 3R, 4, 4X
Insulation	Y
Temperature Rating	105 Degrees C

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	40mm
Nominal size in inch	1 1/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
One-piece	N
Material housing	Stainless steel

Surface protection	Untreated
Total length	103.12mm
Total height	88.39mm
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit CSA	Y
Approved in combination with protective conduit UL	Y
Approved in combination with protective conduit FI	N
Operating temperature	0-105°C

**Packaging**

Inner Quantity	5
Inner Dimensions (inches)	9.5x6.5x4.5
Outer Quantity	25
Outer Dimensions (inches)	23.31x6.81x9.81
Weight Uom	1.19 lbs. Each

**Documents / Support Tools**

3D Rendering	Available on Website
Technical Drawing / Data Sheet	TDS000126
Instruction Sheet	TA05037-TB2
Support/Tools	Available on Website
Marketing Brochure US	Available on Website
Catalog US	Available on Website