



Actual

**Catalog Number:** BEM-2001  
**Product ID:** 7TCA303080R0059  
**UPC Number:** 78621013834  
**EAN Number:** 05415022403572  
**Status:** Active

EMC Cable Gland, Thread Size 2 Inch NPT, Cable Range 34 to 44 Millimeters, Shield Range 30 to 40 Millimeters, Thread Length 22 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	2 Inch NPT
Conductor Range	34 to 44 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 inch
Thread length	22mm
Suitable for cable diameter	34 - 44mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	4
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Technical Drawing / Data Sheet Canada	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website

Thomas & Betts - USA