



Catalog Number: BEM-M202
Product ID: 7TCA303080R0044
UPC Number: 78621013818
EAN Number: 05415022403428
Status: A



Actual

EMC Cable Gland, Thread Size M20, Cable Range 7.5 to 14mm, Shield Range 5.5 to 11.5mm, Thread Length 8mm, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	M20
Conductor Range	7.5 to 14 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	20
Pitch thread	1.5mm
Thread length	8mm
Suitable for cable diameter	7.5 - 14mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	50
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website



Header

3D Model

Available on Website