



Actual

Catalog Number: BEM-PG111
Product ID: 7TCA303080R0061
UPC Number: 78621013837
EAN Number: 05415022403596
Status: Active

EMC Cable Gland, Thread Size PG11, Cable Range 5 to 10 Millimeters, Shield Range 3.5 to 8 Millimeters, Thread Length 6 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	PG11
Conductor Range	5 to 10 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	PG
Nominal thread size metric/PG	11
Thread length	6mm
Suitable for cable diameter	5 - 10mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	100
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Technical Drawing / Data Sheet Canada	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website

Thomas & Betts - USA