

Catalog Number: CPO1500-C-A
Product ID: 7TBA017980R0038
UPC Number: 78621095241
Status: Active



Actual

Heat Shrink Tubing, Clear, 1-1/2 Inch, 4 Foot, Thin Wall

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Brand Name	Shrink-Kon
Type	Heat Shrink Tubing
Shrink Ratio	2:1
Length	4 ft ; 1.22 m
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 Degrees F (-55 C) to 275 Degrees F (135 C)
Minimum Shrink Temperature	248 Degrees F (120 C)
Water Absorption	0.20%
Color	Clear

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	38mm
Inner diameter after heat-shrink	19.05mm
Nominal diameter inch	1 1/2 inch
Wall thickness after shrinking	1.016mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Transparent
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

Packaging

Inner Quantity	10
Inner Dimensions (inches)	1x1x1
Outer Quantity	100
Outer Dimensions (inches)	10x10x10
Weight Uom	1.56 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website