



**Catalog Number:** CPO2000-C-A  
**Product ID:** 7TBA017980R0045  
**UPC Number:** 78621095242  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Clear Cross-Linked Polyolefin, 2 Inch, Shrink Ratio 2:1, Length 4 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

Actual

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	2:1
Length	4 ft ; 1.22 m
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Water Absorption	0.20%
Color	Transparent

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	51mm
Inner diameter after heat-shrink	25.4mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	1.143mm
Length	0.1524m
Operation temperature	-55-+135°C
Colour	Transparent
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	N

**Packaging**

Inner Dimensions (inches)	xx
Outer Quantity	25
Outer Dimensions (inches)	10x10x10
Weight Uom	1.56 lbs. per 100