

**Catalog Number:** CPO63-6-C  
**Product ID:** 7TAA017980R0074  
**UPC Number:** 78621083623  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Blue Cross-Linked Polyolefin, 1/16 Inch, Shrink Ratio 2:1, Length 100 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	100 ft
Color	Blue

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	1.6mm
Inner diameter after heat-shrink	0.762mm
Nominal diameter inch	1/16 inch
Wall thickness after shrinking	0.508mm
Length	30.48m
Operation temperature	-55-+135°C
Colour	Blue
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	9.3x9.2x2.8
Weight Uom	1.53 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2