

Catalog Number: CPO93-6-C
Product ID: 7TAA017980R0088
UPC Number: 78621085381
Status: A



Actual

Thin-Wall Heat Shrinkable Tubing, Blue Cross-Linked Polyolefin, 3/32 Inch, Shrink Ratio 2:1, Length 100 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	100 ft
Color	Blue

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	2.286mm
Inner diameter after heat-shrink	1.27mm
Nominal diameter inch	3/32 inch
Wall thickness after shrinking	0.508mm
Length	30.48m
Operation temperature	-55-+135°C
Colour	Blue
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	16x6.75x16
Weight Uom	275 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website
Safety Data Sheet (SDS) Global	SDS-00046-TB2