



Representative

Catalog Number: CTPA12-S/25M
Product ID: 7TCA298000R0042
EAN Number: 05020963046568
Status: Active

Lightweight Weight, Extra Flexible Slit Conduit, NC Size 12/NW Size 10, Outside Diameter 13.0mm, Inside Diameter 10.1mm, Static Bend Radius 20mm, High Fatigue Life and Abrasion, Impact Resistance, IP40 Rating, Polyamide 6, Reel Length 25 Meters, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5540 Flexible Non-Metallic Conduit
Brand Name	Harnessflex
Type	Slit Lightweight Conduit
Special Features	Self Extinguishing, Low Smoke Toxicity & Halogen Free
Application	General Purpose, Lightweight Loom Applications
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV)EU200/53/EC
Trade Size	NC12/NW10
Outside Diameter	13.0mm
Inside Diameter	10.1mm
Length	25 m
Radius	Static Bend Radius 20mm
Flexibility	High
Material	Polyamide/Nylon 6
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	12mm
Nominal size in inch	5/16 inch
Outer diameter	13mm
Inner diameter	10.1mm
Material	Polyamide 6
Operating temperature	-40-+120°C
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	Y
Halogen free	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	1.32 lbs. Each

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com