

Catalog Number: CTPA25-S/100M
Product ID: 7TCA298000R0101
EAN Number: 05020963046650
Status: Active

Lightweight Weight, Extra Flexible Slit Conduit, NC Size 25/NW Size 22, Outside Diameter 25.6mm, Inside Diameter 21.3mm, Static Bend Radius 45mm, High Fatigue Life and Abrasion, Impact Resistance, IP40 Rating, Polyamide 6, Reel Length 100 Meters, Black

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5540 Flexible Non-Metallic Conduit
Brand Name	Harnessflex
Type	Slit Lightweight Conduit
Special Features	Self Extinguishing, Low Smoke Toxicity & Halogen Free
Application	General Purpose, Lightweight Loom Applications
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV)EU200/53/EC
Trade Size	NC25/NW22
Outside Diameter	25.6mm
Inside Diameter	21.3mm
Length	100 m
Radius	Static Bend Radius 45mm
Flexibility	High
Material	Polyamide/Nylon 6
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	25mm
Nominal size in inch	3/4 inch
Outer diameter	25.6mm
Inner diameter	21.3mm
Material	Polyamide 6
Operating temperature	-40-+120°C
Degree of protection (IP)	IP40
Fire resistance in accordance with UL94	HB
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	Y
Halogen free	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	11.46 lbs. Each

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

