



Family

Catalog Number: CYFHG-29B.50
Product ID: 7TAA292240R0001
UPC Number: 78620995450
EAN Number: 07630030224171
Status: Active

Heavy Wall Flexible Black Conduit, (CYFH) Material - Polyamide 6, Conduit Size NW - 29, 50 Meters

- Good flexibility
- Good impact strength, also at low temperatures and dry conditions
- Self-extinguishing, free from halogens and cadmium
- Automobile and truck industries

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Heavy Duty Conduit
Application	Vehicle Building
Trade Size	NW29
Length	50 m
Flexibility	Medium Flexibility
Material	Polyamide/Nylon 6
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	32mm
Outer diameter	34.4mm
Inner diameter	27.2mm
Material	Polyamide 6
Compressive strength	300N
Operating temperature	-30 - +90°C
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	N
Halogen free	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	N
Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

Packaging

Inner Quantity	1
Outer Quantity	6
Outer Dimensions (inches)	47.244x31.496x29.528
Weight Uom	0.11 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com