

**Catalog Number:** M25CLF020-6E2  
**Product ID:** 7TAA124320R0016  
**UPC Number:** 78378697609  
**Status:** Active

Encapsulated Molded Current-Limiting Fuses, Nominal Fuse Voltage Rating 15.5kV, Current Rating Amps 20, Option 6E2 - 600 Amp Elbow connector on one end and a 200 Amp Bushing Well on the other end

**North American Specifications (UNSPSC)**

UNSPSC	39121626 Medium voltage fuse
IGCC	4980 Medium voltage fuse
Brand Name	Elastimold
Type	Current Limiting Fuse
Special Features	EPDM Molded Rubber Deadfront Construction Insulates, Shields and Eliminates Exposed Live Parts. Lightweight Fuses are Fully Sealed and Submersible. Specially Designed Fuse Elements with Built-in Low and High Current Interrupting Capability Provide Full Range Fault Current Protection thru 50kA. Current Limiting Protection limits the System Available Fault Current and Dramatically reduces Stresses on Equipment. Internal Fuse Shield Prevents Corona and Deterioration of the Fuse Element.
Application	Suitable for Padmount, Subsurface or Vault Installations
Standard	ANSI C37.40, ANSI C37.41, ANSI C37.47, IEEE 386
Amperage Rating	20 Amps
Voltage Rating	15.5 kV
Mounting	Clip
Material	EPDM Molded Rubber

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	1 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com