



Actual

**Catalog Number:** RBCG-M164  
**Product ID:** 7TCA303080R0005  
**UPC Number:** 78621011980  
**EAN Number:** 05415022395839  
**Status:** Active

Non Armoured Cable Gland for Rail, Thread Size M16, Cable Range 5 to 10 Millimeters, Thread Length 12 Millimeters, Nickel Plated Brass

- EN 45545-2 Compliant HL3 for category R22 and R23 usage
- Robust metallic construction
- Large capacity sealing range
- R22 interior locations for small components
- R23 exterior locations for small components

### North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Non Armoured Cable Gland for Rail
Application	To Connect Conduit to an Opening or Enclosure
Standard	RoHS, WEEE, LVD
Size	M16
Conductor Range	5 to 10 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
Temperature Rating	-40 to +100 Degrees C

### European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	16
Pitch thread	1.5mm
Thread length	12mm
Suitable for cable diameter	5 - 10mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-40-+100°C

### Packaging

Inner Quantity	10
Outer Quantity	100
Outer Dimensions (inches)	7.09x3.54x3.54
Weight Uom	0.1 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000042
Technical Drawing / Data Sheet Canada	TDS000042
Instruction Sheet	TA05283-TB2
Support/Tools	Available on Website

Thomas & Betts - USA