



Actual

**Catalog Number:** SB10/25M  
**Product ID:** 7TCA296040R0014  
**EAN Number:** 05020963061271  
**Status:** Active

Low Fire Hazard, High Flexibility, Covered Steel Conduit, Nominal Conduit Size 10mm, Outside Diameter 10.0mm, Inside Diameter 6.8mm, Static Bend Radius 25mm, Reel Length 25 Meters, Galvanised Steel Core and Overbraid

- Very high UV resistance
- High flexibility
- High fatigue life
- High mechanical strength, high abrasion resistance
- Inherent low fire hazard and halogen free
- Enhanced EMI screen rating
- Industrial

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	Low Fire Hazard Conduit
Special Features	Very High UV Protection and High Fatigue Life
Application	Indoors / Outdoors - Standard EMI Screen - Very High Abrasion Resistance
Trade Size	1/4 Inch/10mm
Outside Diameter	10.0mm
Inside Diameter	6.8mm
Length	25 Meters
Radius	25mm
Flexibility	High
Material	Galvanized Steel Core and Overbraid

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	10mm
Outer diameter	10mm
Inner diameter	6.8mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Steel wire, galvanized
Operating temperature	-50-+300°C
Degree of protection (IP)	IP40
Weight	0.1kg/m
Colour	Metallic
Bending strength	Flexible

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	11.13 lbs. Each

### Header

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)