



Actual

**Catalog Number:** SP50/BL/10M  
**Product ID:** 7TCA296020R0288  
**EAN Number:** 05020963000461  
**Status:** Active

Liquid Resistant, General Purpose, Highly Flexible Conduit, Nominal Conduit Size 50mm, Outside Diameter 55.0mm, Inside Diameter 48.4mm, Static Bend Radius 90mm, Reel Length 10 Meters, PVC Jacket with Galvanised Steel Core, Black

- Very high UV resistance
- High flexibility
- Medium fatigue life
- High mechanical strength
- Self extinguishing

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	High Flexibility Conduit
Application	Indoors / Outdoors - Light Industrial, General Purpose, Buildings
Trade Size	1-1/2 Inch
Outside Diameter	55.0mm
Inside Diameter	48.4mm
Length	10 Meters
Radius	90mm
Flexibility	High
Material	Galvanized Steel Core with PVC Jacket
Color	Black

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	50mm
Outer diameter	55mm
Inner diameter	48.4mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Operating temperature	-25-+70°C
Degree of protection (IP)	IP65
Weight	1.166kg/m
Colour	Black
Bending strength	Flexible

### Packaging

Inner Quantity	2
Inner Dimensions (inches)	16x17x16
Outer Quantity	2
Outer Dimensions (inches)	16x17x16
Weight Uom	25.49 lbs. Each

### Header

3D Model Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)