



Actual

Catalog Number: SPLHCB20/25M
Product ID: 7TCA296100R0170
EAN Number: 05020963011955
Status: Active

Liquid Tight, Extreme Temperature Covered Steel Flexible Conduit with Stainless Steel Overbraid, Medium Flexibility, Nominal Conduit Size 20mm, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 25 Meters, Thermoplastic Rubber Cover with Galvanised Steel Core, Black

- Very high UV resistance
- Very high flexibility
- Very high fatigue life
- High mechanical strength, high abrasion resistance
- Self extinguishing and halogen free
- Standard EMI screen rate
- Rail/Infrastructure
- Underground
- Public Buildings

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5543 Liquid Tight Conduit
Brand Name	Adaptaflex
Type	Extreme Temperature Flexible Conduit
Application	Liquid Tight - Extreme Temperature Environments
Trade Size	1/2 Inch/NC 20mm
Outside Diameter	21.1mm
Inside Diameter	15.9mm
Length	25 Meters
Radius	80mm
Flexibility	Medium
Material	Galvanized Steel Core with Thermoplastic Rubber Cover
Color	Black

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	20mm
Outer diameter	21.1mm
Inner diameter	15.9mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	Other
Sheathing material 2nd coating (exterior)	Stainless steel wire
Operating temperature	-65-+135°C
Degree of protection (IP)	IP68
Weight	0.385kg/m
Colour	Black
Bending strength	Flexible

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1

Weight Uom

21.22 lbs. Each

Header

3D Model

Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com