



Actual

**Catalog Number:** SPTC25/25M  
**Product ID:** 7TCA296100R0185  
**EAN Number:** 05020963010866  
**Status:** Active

Highly Flexible Conduit, Nominal Conduit Size 25mm, Outside Diameter 26.0mm, Inside Diameter 21.4mm, Static Bend Radius 55mm, Reel Length 25 Meters, Galvanised Steel Core with PVC Jacket and Tinned Copper Overbraid, Black

- Very high UV resistance
- High flexibility
- Medium fatigue life
- High mechanical, high abrasion resistance
- Self extinguishing
- High EMI screen rate
- Machine Building
- External Safety Critical Areas
- Hospitals

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Adaptaflex
Type	High Flexibility Conduit
Special Features	Very High UV Protection
Application	Indoors / Outdoors - Enhanced EMI Screen - High Abrasion Resistance
Trade Size	3/4 Inch
Outside Diameter	26.0mm
Inside Diameter	21.4mm
Length	25 m
Radius	55mm
Flexibility	High
Material	Galvanized Steel Core, Tinned Copper Overbraid with PVC Jacket
Color	Black

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal diameter	25mm
Outer diameter	26mm
Inner diameter	21.4mm
Material	Steel
Surface protection	Other
Sheathing material 1st coating	PVC
Sheathing material 2nd coating (exterior)	Other
Operating temperature	-15-+70°C
Degree of protection (IP)	IP54
Weight	0.28kg/m
Colour	Black
Bending strength	Flexible

### Packaging

Outer Quantity	1
----------------	---

Outer Dimensions (inches)	1x1x1
Weight Uom	19.46 lbs. Each

**Header**

3D Model	Available on Website
----------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)