

Catalog Number: CPO500-0-A
Product ID: 7TAA017310R0182
UPC Number: 78621083504
Status: A



Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 1/2 Inch, Shrink Ratio 2:1, Length 4 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Voltage Rating	600 V
Thickness	Thin
Length	4 ft
Color	Black

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	12.7mm
Inner diameter after heat-shrink	6.35mm
Nominal diameter inch	1/2 inch
Wall thickness after shrinking	0.762mm
Length	1.22m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Inner Quantity	25
Inner Dimensions (inches)	1x1x1
Outer Quantity	250
Outer Dimensions (inches)	50.5x11x8.5
Weight Uom	6.25 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website