

Catalog Number: CPO1000-5-C
Product ID: 7TAA017310R0021
UPC Number: 78621098640
Status: A



Thin-Wall Heat Shrinkable Tubing, Green Cross-Linked Polyolefin, 1 Inch, Shrink Ratio 2:1, Length 100 Feet, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637; DEF STAN 59-97, Issue 3, Type 2a

Actual

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Flame-retardant, cross-linked polyolefin.
Shrink Ratio	2:1
Thickness	Thin
Length	100 ft
Color	Green

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	25.4mm
Inner diameter after heat-shrink	12.7mm
Nominal diameter inch	1 inch
Wall thickness after shrinking	10.16mm
Length	30.48m
Operation temperature	-55-+135°C
Colour	Green
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	13.3x13.3x3.9
Weight Uom	2.35 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website