



**Catalog Number:** CPO2000-0-25  
**Product ID:** 7TAA017310R0107  
**UPC Number:** 78620992886  
**Status:** A



Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 2 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

Actual

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Shrink Ratio	2:1
Thickness	Thin
Length	25 ft ; 7.62 m
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Flammability	Flame Retardant
Water Absorption	0.20%
Color	Black

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	51mm
Inner diameter after heat-shrink	25.4mm
Nominal diameter inch	2 inch
Wall thickness after shrinking	1.143mm
Length	7.62m
Operation temperature	-55-+135°C
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	5.8x5.8x1.8
Weight Uom	2.22 lbs. Each