



Family

Catalog Number: CHS18B
Product ID: 7TAA017340R0009
UPC Number: 78621080295
Status: A

Thin-Wall Heat-Shrinkable Tubing for Cable Range 22 - 18 AWG, Expanded Diameter 0.13 inch, Reel of 250 Feet, rated for 600 Volt, 125 degrees C, Material: Polyvinyl Chloride, Clear

- Clear shrink enables user to inspect die and crimp details after installation.
- Flexible PVC tubing is suitable for industrial and electronic applications.
- UL standard UL224, VW-1 Rated. CSA standard C22.2 no. 198.1 oft.

North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Thin-Wall Heat Shrinkable Tubing
Special Features	Clear shrink enables user to inspect die and crimp details after installation.
Shrink Ratio	2:1
Thickness	Thin
Length	250 ft
Color	Transparent

European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	3.302mm
Inner diameter after heat-shrink	1.524mm
Nominal diameter inch	1/8 inch
Wall thickness after shrinking	0.508mm
Length	76.2m
Operation temperature	-30-+105°C
Colour	Transparent
Material	PVC
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

Packaging

Outer Quantity	1
Outer Dimensions (inches)	16x16x6.75
Weight Uom	4 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website