



Actual

Catalog Number: CPO750-0-25
Product ID: 7TAA017300R0252
UPC Number: 78621085128
Status: A

Thin-Wall Heat Shrinkable Tubing, Black Cross-Linked Polyolefin, 3/4 Inch, Shrink Ratio 2:1, Length 25-Foot Reel, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined

- Flame-retardant, cross-linked polyolefin.
- Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C; MIL-DTL-23053/5 Class 1&#amp;2; AMS 3636 &#amp;2; 3637; DEF STAN 59-97, Issue 3, Type 2a

North American Specifications (UNSPSC)

| | |
|------------------|---|
| UNSPSC | 39121723 Heat shrinkable tube |
| IGCC | 5073 Heat shrinkable tube |
| Type | Thin-Wall Heat Shrinkable Tubing |
| Special Features | Flame-retardant, cross-linked polyolefin. |
| Voltage Rating | 600 V |
| Thickness | Thin |
| Length | 25 ft |
| Color | Black |

European Specifications (ETIM)

| | |
|-----------------------------------|------------------------|
| ETIM | EC000217 Shrink tubing |
| Type | Heat-shrink |
| Model | Thin-walled |
| Shrink rate | 2:1 |
| Inner diameter before heat-shrink | 19.05mm |
| Inner diameter after heat-shrink | 9.652mm |
| Nominal diameter inch | 3/4 inch |
| Wall thickness after shrinking | 0.762mm |
| Length | 7.62m |
| Operation temperature | -55-+135°C |
| Colour | Black |
| Material | Polyolefin (PO-X) |
| Halogen free | N |
| With inner glue | N |
| Printable | N |
| UL approval | Y |

Packaging

| | |
|---------------------------|-----------------|
| Inner Quantity | 1 |
| Outer Quantity | 10 |
| Outer Dimensions (inches) | 13.4x13.3x6.7 |
| Weight Uom | 74 lbs. per 100 |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Catalog Page | Available on Website |
| Safety Data Sheet (SDS) Global | SDS-00046-TB2 |