

**Catalog Number:** CPO750-2-6  
**Product ID:** 7TAA017310R0243  
**UPC Number:** 78620988316  
**Status:** A

Thin-Wall Heat Shrinkable Tubing, Red Cross-Linked Polyolefin, 3/4 Inch, Shrink Ratio 2:1, Length 6 Inches, Operating Temperature -55 to 135 Degrees Celsius, Non-Lined



Actual

### North American Specifications (UNSPSC)

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	2:1
Length	6 in ; 152.4 mm
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Flammability	Flame Retardant
Water Absorption	0.20%
Color	Red

### European Specifications (ETIM)

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	9.652mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	0.762mm
Length	0.1524m
Operation temperature	-55-+135°C
Colour	Red
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x8x8
Outer Quantity	100
Outer Dimensions (inches)	10.5x12.8x8.1
Weight Uom	10.63 lbs. per 1000

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Catalog Page	Available on Website