



**Catalog Number:** CPO-A-750-2-48  
**Product ID:** 7TAA017320R0030  
**UPC Number:** 78621073946  
**Status:** A



Actual

Thin-Wall Heat Shrinkable Tubing, Red Polyolefin, 3/4 Inch, Shrink Ratio 3:1, Length 48 Inches, Operating Temperature -55 to 110 Degrees Celsius, Adhesive Lined

**North American Specifications (UNSPSC)**

UNSPSC	39121723 Heat shrinkable tube
IGCC	5073 Heat shrinkable tube
Type	Heat Shrinkable Tubing
Shrink Ratio	3:1
Length	4 ft ; 1.22 m
Dielectric Strength	600 V/Mil (24kV/mm)
Volume Resistivity	1016 ohm-cm
Continuous Operating Temperature	-67 to +275 F ; -55 to +135 C
Minimum Shrink Temperature	248 F ; 120 C
Flammability	Flame Retardant
Water Absorption	0.20%
Color	Red

**European Specifications (ETIM)**

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	3:1
Inner diameter before heat-shrink	19.05mm
Inner diameter after heat-shrink	7.874mm
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	1.778mm
Length	1.22m
Operation temperature	-55-+110°C
Colour	Red
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	Y
Printable	N
UL approval	N

**Packaging**

Inner Quantity	10
Inner Dimensions (inches)	1x.5x.1
Outer Quantity	100
Outer Dimensions (inches)	4x51x4
Weight Uom	37.5 lbs. per 100