



Catalog Number: HSMW1300-48
Product ID: 7TAA017210R0002
UPC Number: 78621091615
Status: A



Medium-Wall Heat-Shrinkable Tubing for Cable Range , Expanded Diameter 1.3, Length 48 inch, rated for 600 Volt, 90 degrees continuous use, Material: Cross-linked polyolefin with thermoplastic adhesive liner, Black

- More flexible than heavy-wall products. Seals and protects cable splices and terminations.
- Thermoplastic Adhesive Liner for complete environment protection and insulation.
- High resistance to impact and abrasion.

Actual

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39121723 Heat shrinkable tube |
| IGCC | 5073 Heat shrinkable tube |
| Type | Medium-Wall Heat Shrinkable Tubing |
| Special Features | More flexible than heavy-wall products. Seals and protects cable splices and terminations. |
| Shrink Ratio | 3:1 |
| Length | 48 in |
| Color | Black |

European Specifications (ETIM)

| | |
|-----------------------------------|------------------------|
| ETIM | EC000217 Shrink tubing |
| Type | Heat-shrink |
| Model | Medium-walled |
| Shrink rate | 3:1 |
| Inner diameter before heat-shrink | 33.02mm |
| Inner diameter after heat-shrink | 10.16mm |
| Nominal diameter inch | Other |
| Wall thickness after shrinking | 2.412mm |
| Length | 1.22m |
| Operation temperature | -55-+110°C |
| Colour | Black |
| Material | Polyolefin (PO-X) |
| Halogen free | N |
| With inner glue | Y |
| Printable | N |
| UL approval | N |

Packaging

| | |
|---------------------------|-----------------|
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 6x49x19 |
| Weight Uom | 45 lbs. per 100 |

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website