



Actual

Catalog Number: 696-41794
Product ID: 7TAA159090R0000
UPC Number: 78621007039
EAN Number: 05414363145646
Status: A

Deltec Cable Tie Without Double-Locking Head, Black Acetal for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant, Length of 304.8m (1000 Foot) Reel, Width of 12.7mm (0.5 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length, Special Pack

- Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
- Strap and body are weatherable acetal, offering superior resistance to sunlight, moisture and salt environments.
- Locking device is marine-grade corrosion-resistant copper alloy.
- Application Tools: WT3D

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Type	Strap on a Reel
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.
Width	0.5 in ; 12.7 mm
Material	Weather Resistant Acetel
Color	Black
Tensile Strength	250 pounds ; 1112 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	12.7mm
Length belt/tape/tie	304.8mm
Tie thickness	1.52mm
Min. holding force	1112N
Operating temperature	-40-+105°C
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyoxymethylene (POM)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N

Packaging

Outer Quantity	1
Outer Dimensions (inches)	12.8x10.5x10.3
Weight Uom	1720 lbs. per 100



Documents / Support Tools

Technical Drawing / Data Sheet US

[Available on Website](#)