



Actual

Project: MES
Location: Indianapolis

Standard Electric Supply
 9900 Westpoint Drive
 Ste 142
 Indianapolis, IN 46112

Catalog Number: BEM-1501
Product ID: 7TCA303080R0058
UPC Number: 78621013833
EAN Number: 05415022403565
Status: A

EMC Cable Gland, Thread Size 1-1/2 Inch NPT, Cable Range 30 to 38 Millimeters, Shield Range 26 to 34 Millimeters, Thread Length 22 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	1-1/2 Inch NPT
Conductor Range	30 to 38 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	4
Temperature Rating	-20 to +100 C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 1/2 inch
Thread length	22mm
Suitable for cable diameter	30 - 38mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity 5

Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	5
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website

Header

3D Model	Available on Website
----------	----------------------