



Actual

Catalog Number: BEM-1001
Product ID: 7TCA303080R0056
UPC Number: 78621013831
EAN Number: 05415022403541
Status: Active

EMC Cable Gland, Thread Size 1 Inch NPT, Cable Range 16 to 25 Millimeters, Shield Range 12 to 20 Millimeters, Thread Length 20 Millimeters, Nickel Plated Brass

- Low profile compact cable glands
- Wide cable clamping range
- Good corrosion resistance
- Extended radial contact with the shielding for improved EMI protection

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	EMC Cable Gland
Application	General purpose, Panel building, Light fixture and housings
Standard	cULus, RoHS, WEEE, LVD
Size	1 Inch NPT
Conductor Range	16 to 25 Millimeters
Material	Brass
Finish	Nickel Plated
Color	Metallic
NEMA Rating	NEMA 4
Temperature Rating	-20 to +100 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	1 inch
Thread length	20mm
Suitable for cable diameter	16 - 25mm
Material	Metal
Material quality	Brass
Surface protection	Nickel-plated
Degree of protection (IP)	IP68
Colour	Natural colour
Model	Straight
Operating temperature	-20-+100°C
EMC-version	Y

Packaging

Inner Quantity	10
Inner Dimensions (inches)	7.09x3.54x3.54
Outer Quantity	10
Outer Dimensions (inches)	3.94x15.75x11.02
Weight Uom	0.01 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000033
Technical Drawing / Data Sheet Canada	TDS000033
Instruction Sheet	TA05286-TB2
Support/Tools	Available on Website

Thomas & Betts - USA