


Engineered-Performance Material Cable Ties

Extra high temperatures!

Ty-Rap® Extra High-Temperature 4.6 Nylon Ties



For use in temperatures ranging from -40° F to 302° F (-40° to 150° C).

Color — Natural (Olive)

- Non-hydroscopic stainless steel barb will not weaken or wear out after years of environmental stress
- Smooth, notchless body reduces stress, increasing life expectancy over standard notched, one-piece cable ties
- Quicker to install and less expensive than metallic fasteners, lacing cord or tape
- Ideal for Industrial applications including metal processing, paper mills, lighting and commercial construction markets with high temperature environments up to 302° F (150° C)
- Provides a smooth, low-profile look and unlimited tensioning range for a perfect fit
- Features an oval head on every original Ty-Rap® Cable Tie



BULK PKG. CAT. NO.	LENGTH IN./MM	TENSILE STRENGTH LBS./N	BULK PKG. QTY.
TYHT23M	3.62/91.95	18/80.07	1,000
TYHT25M	7.31/185.67	50/222.40	1,000
TYHT27M	13.40/340.36	120/533.80	500
TYHT28M	14.20/360.68	50/222.40	1,000

Engineered to withstand high temperatures!

Ty-Rap® Heat-Stabilized Natural 6.6 Nylon Ties



For use in temperatures ranging from -40° F to 221° F (-40° C to 105° C).

Material meets ASTM D4066 PA121.

Color — Green Tint



BULK PKG. CAT. NO.	WIDTH IN./MM	BODY LENGTH IN./MM	MAX. WIRE BUNDLE DIA. IN./MM	TENSILE STRENGTH LBS./N	BULK PKG. QTY.
TYH23M	.09/2.29	3.62/91.95	.63/16.00	18/80.07	1,000
TYH232M	.09/2.29	8.00/203.20	2.00/50.80	18/80.07	1,000
TYH24M	.14/3.56	5.50/139.70	1.13/28.70	40/177.90	1,000
TYH242M	.14/3.56	8.19/208.03	2.00/50.80	40/177.90	1,000
TYH26M	.14/3.56	11.10/281.94	3.00/76.20	30/135	1,000
TYH25M	.18/4.57	7.31/185.67	1.75/44.45	50/222.40	1,000
TYH253M	.18/4.57	11.40/289.56	3.00/76.20	50/222.40	1,000
TYH28M	.18/4.57	14.20/360.68	4.00/101.60	50/222.40	1,000
TYH27M	.27/6.86	13.20/335.28	3.50/88.90	120/533.80	500
TYH272M	.27/6.86	8.75/222.25	2.00/50.80	120/533.80	500
TYH29M	.30/7.62	30.00/762.00	9.00/228.60	120/533.80	500

Perfect for outdoor applications!

Ty-Rap® Heat-Stabilized/UV-Resistant Black 6.6 Nylon Ties



For use in temperatures ranging from -40° F to 221° F (-40° C to 105° C)

Color — Black



- Non-hydroscopic stainless steel barb will not weaken or wear out after years of environmental stress
- Smooth, notchless body reduces stress, increasing life expectancy over standard notched, one-piece cable ties
- Ideal for Industrial applications including lawn/garden/farming equipment, recreation vehicles and heavy equipment
- Can be placed in environments requiring heat stabilization and UV resistance
- Provides a smooth, low-profile look and unlimited tensioning range for a perfect fit
- Features an oval head on every original Ty-Rap® Cable Tie
- Quicker to install and less expensive than metallic fasteners, lacing cord or tape



BULK PKG. CAT. NO.	LENGTH IN./MM	TENSILE STRENGTH LBS./N	BULK PKG. QTY.
TY23MX-A	3.62/91.95	18/80.07	1,000
TY24MX-A	5.50/139.70	40/177.90	1,000
TY25MX-A	7.31/185.67	50/222.40	1,000
TY28MX-A	14.20/360.68	50/222.40	1,000
TY27MX-A	13.40/340.36	120/533.80	500