


HYDRAULIC TELESCOPING BOOM- LM-1T-8-24-HBE-DC

APPROX WEIGHT: 796.74 lbs.
DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS LM-1T-8-24-HBE-DC
 MAXIMUM MOVABLE LOAD IS 2,000 LBS.
 LOST LOAD - 815 LBS.
 OVERALL HEIGHT - 24 1/2"
 LENGTH RETRACTED - 83 3/4"
 LENGTH EXTENDED - 144 3/4"

OVERALL WIDTH - 32"
 36" MINIMUM HOOK POINT
 142" MAXIMUM HOOK POINT
 12V DC POWER UNIT TO EXTEND/RETRACT BOOM
 W/ HAND CONTROL ON AN 8' CORD
 BOOM CAN BE EXTENDED/RETRACTED WHILE LOADED
 USABLE FORK POCKETS - 7 1/4" X 2 1/4"
 24" FORK POCKET CENTERS
 EFFECTIVE THICKNESS: LESS THAN 1"
 REQUIRES 8,000 LB RATED FORK TRUCK
 FRAME IS DURABLE LIQUID PAINT BLUE FINISH
 BOOM IS DURABLE LIQUID PAINT YELLOW FINISH

SPECIAL FEATURES

NONE

*--MAXIMUM SINGLE HOOK CAPACITIES

DISTANCE	36"	48"	60"	72"	84"	96"	108"	120"	132"	142"
CAPACITY	8000	6650	6000	5300	4650	4000	3500	3000	2600	2200

DIMENSION TOLERANCE ± 1/4"

APPROVAL

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

[] As drawn [] As marked

Signed: _____ Date: _____

Printed Name: _____

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

NEVER EXCEED LOAD CENTER RATING PER FORK TRUCK MANUFACTURER'S GUIDELINES.
 DO NOT USE THIS FORK TRUCK ATTACHMENT IF LOAD WILL EXCEED FORK TRUCK MANUFACTURER'S LOAD CENTER RATING

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
DRAWN BY: KGH		W.O.#
DATE: 2/6/2019		X
REFERENCE: X	SCALE: 1:20	SALES: X
QUOTED LEAD TIME: X	QUOTE # X	FILE NAME:
		08-007-398