



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : W22 Brake Motor - NEMA Premium Efficiency

Frame : 143/5T
Output : 1 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1150 rpm
Slip : 4.17 %
Voltage : 208-230/460 V
Rated current : 3.82-3.45/1.73 A
Locked rotor current : 21.4/10.7 A
Locked rotor current (I_L/I_N) : 6.2
No-load current : 2.39/1.20 A
Full load torque : 4.51 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 300 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 28 s (hot)
Service factor : 1.25
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 58 lb
Moment of inertia : 0.15947 sq.ft.lb
Noise level : 49 dB(A)

	D.E.	N.D.E.
Bearings	6205 ZZ	6204 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.66	82.5
75%	0.57	82.0
50%	0.45	77.0

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #00112ET3EBM145T-W22

Performed by

Checked