



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Close Coupled Pump : Three-Phase - "JM" Type - ODP - NEMA Premium

Frame : E143/5JM
Output : 1 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1730 rpm
Slip : 3.89 %
Voltage : 208-230/460 V
Rated current : 3.00-2.90/1.45 A
Locked rotor current : 23.2/11.6 A
Locked rotor current (I_L/I_N) : 8.0
No-load current : 2.00/1.00 A
Full load torque : 2.99 lb.ft
Locked rotor torque : 320 %
Breakdown torque : 330 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 15 s (hot)
Service factor : 1.15 (1.00 at 208V)
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP21
Approximate weight : 37 lb
Moment of inertia : 0.12411 sq.ft.lb
Noise level : ---

	D.E.	N.D.E.
Bearings	6206 ZZ	6204 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.76	85.5
75%	0.68	85.5
50%	0.54	82.5

Notes:

Downloaded from <http://dealersselectric.com>
Generated for Model #00118OT3E143JM

Performed by

Checked