



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET Single-phase induction motor - Squirrel cage rotor

Customer :
 Product line : Single Phase: W01 (Rolled Steel) - ODP - Premium Efficiency (DOE)

Frame : 56
 Output : 1 HP
 Frequency : 60 Hz
 Poles : 2
 Full load speed : 3510 rpm
 Slip : 2.50 %
 Voltage : 115/208-230 V
 Rated current : 8.60/4.75-4.30 A
 Locked rotor current : 72.2/36.1 A
 Locked rotor current (I_L/I_n) : 8.4
 No-load current : 2.60/1.30 A
 Full load torque : 1.48 lb.ft
 Locked rotor torque : 290 %
 Breakdown torque : 300 %
 Design : ---
 Insulation class : F
 Temperature rise : 80 K
 Locked rotor time : 16 s (hot)
 Service factor : 1.25
 Duty cycle : S1
 Ambient temperature : -20°C - +40°C
 Altitude : 1000 m
 Degree of Protection : ODP
 Approximate weight : 30 lb
 Moment of inertia : 0.05505 sq.ft.lb
 Noise level : 58 dB(A)

	D.E.	N.D.E.
Bearings	6204 ZZ	6202 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.94	80.4
75%	0.93	76.0
50%	0.89	69.0

Notes:
 Downloaded from <http://dealerselectric.com>
 Generated for Model #00136OT1B56-S

Performed by

Checked