



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 143T
Output : 1 HP
Frequency : 60 Hz
Poles : 2
Full load speed : 3495 rpm
Slip : 2.92 %
Voltage : 208-230/460 V
Rated current : 3.13-2.83/1.41 A
Locked rotor current : 25.4/12.7 A
Locked rotor current (I_L/I_N) : 9.0
No-load current : 1.50/0.750 A
Full load torque : 1.48 lb.ft
Locked rotor torque : 300 %
Breakdown torque : 400 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 40 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 62 lb
Moment of inertia : 0.04153 sq.ft.lb
Noise level : 68 dB(A)

	D.E.	N.D.E.
Bearings	6205 2RS	6204 2RS
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.82	81.5
75%	0.76	80.0
50%	0.65	75.5

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #00136XT3E143T

Performed by

Checked