



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET

Single-phase induction motor - Squirrel cage rotor

Customer :
Product line : Single Phase: W01 (Rolled Steel) - TEFC - Standard Efficiency

Frame : 56H
Output : 1.5 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1745 rpm
Slip : 3.06 %
Voltage : 115/208-230 V
Rated current : 15.0/8.27-7.48 A
Locked rotor current : 120/59.8 A
Locked rotor current (I_L/I_N) : 8.0
No-load current : 8.50/4.25 A
Full load torque : 4.45 lb.ft
Locked rotor torque : 250 %
Breakdown torque : 270 %
Design : ---
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 8 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 43 lb
Moment of inertia : 0.14262 sq.ft.lb
Noise level : 54 dB(A)

	D.E.	N.D.E.
Bearings	6204 ZZ	6202 ZZ
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.83	77.0
75%	0.78	75.0
50%	0.68	69.0

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #00158ES1B56C-S

Performed by

Checked