



# Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

## DATA SHEET

### Three-phase induction motor - Squirrel cage rotor

Customer :  
 Product line : Close Coupled Pump : Three-Phase - "JM" Type - ODP - High Efficiency

Frame : E143/5JM  
 Output : 1.5 HP  
 Frequency : 60 Hz  
 Poles : 4  
 Full load speed : 1730 rpm  
 Slip : 3.89 %  
 Voltage : 575 V  
 Rated current : 1.68 A  
 Locked rotor current : 13.1 A  
 Locked rotor current (I<sub>L</sub>/I<sub>n</sub>) : 7.8  
 No-load current : 0.960 A  
 Full load torque : 4.49 lb.ft  
 Locked rotor torque : 300 %  
 Breakdown torque : 300 %  
 Design : B  
 Insulation class : F  
 Temperature rise : 80 K  
 Locked rotor time : 15 s (hot)  
 Service factor : 1.15  
 Duty cycle : S1  
 Ambient temperature : -20°C - +40°C  
 Altitude : 1000 m  
 Degree of Protection : IP21  
 Approximate weight : 42 lb  
 Moment of inertia : 0.14238 sq.ft.lb  
 Noise level : ---

	D.E.	N.D.E.	Load	Power factor	Efficiency (%)
Bearings	6206 ZZ	6204 ZZ	100%	0.79	84.0
Regreasing interval	---	---	75%	0.70	84.0
Grease amount	---	---	50%	0.57	82.5

Notes:  
 Downloaded from <http://dealerselectric.com>  
 Generated for Model #00158OP3H145JM

Performed by

Checked