



Dealers Industrial Equipment

No.:

Date: 12-SEP-2016

DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 145T
Output : 1.5 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1760 rpm
Slip : 2.22 %
Voltage : 208-230/460 V
Rated current : 4.53-4.10/2.05 A
Locked rotor current : 36.5/18.2 A
Locked rotor current (I_L/I_n) : 8.9
No-load current : 2.64/1.32 A
Full load torque : 4.42 lb.ft
Locked rotor torque : 270 %
Breakdown torque : 350 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 14 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 71 lb
Moment of inertia : 0.13028 sq.ft.lb
Noise level : 51 dB(A)

	D.E.	N.D.E.
Bearings	6205 2RS	6204 2RS
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.78	86.5
75%	0.70	85.5
50%	0.58	81.5

Notes:
Downloaded from <http://dealerselectric.com>
Generated for Model #00158XT3ER145TC

Performed by

Checked