

Discharge Oil Mist Filters

HDL Series 3" - 8"

Benefits



- Large oil holding capacity and easy field maintenance
- Pleated filter element provides increased surface area for low back pressure separation of ultra-fine oil mists
- Multiple separation stages in single element design
- Waste oil can be recycled

Features

- Captures oil fog, mist or aerosol from exhaust of oil sealed vacuum pumps
- O-ring sealed housings
- Corrosive resistant white powder coat carbon steel
- 1/2" NPT for external drain

Technical Specifications

- 0.3 micron media; 99.97% efficiency
- Continuous operating temp: 68°F (20°C) up to 180°F (80°C)
- Mounted vertically
- Pressure rating: 14.5 PSI



125/150# Pattern Flange	Dimensions (inches)			Number of Holes	Flange Thickness (inches)
	O.D.	B.C.	B.H.		
8"	13.5	11.75	0.88	8	0.38



MPT Inlet / Outlet	Assembly SCFM Rating	Assembly Part Number	Dimensions (inches)				Suggested Service Height (inches)	Approx. Weight (lbs)
			A	B	C	D		
3"	300	HDL-PSG344/2-300	29.50	9.00	12.00	22.50	15	75
4"	500	HDL-PSG344/2-400	29.34	9.00	12.00	22.50	15	78
5"	800	HDL-PSG474/2-500	36.50	11.00	16.00	29.50	22	160
6"	1100	HDL-PSG474/2-600	37.50	12.00	16.00	30.50	22	160
8" Flange	1800	HDL-PSG476-800F	37.25	14.00	20.00	25.50	22	180

Learn More

For more information about Solberg products and finding the right solutions for your equipment needs, visit us at SolbergMfg.com.

Contact Us

solbergmfg.com/locations

