

**Schedule 80 CPVC Industrial Products & Accessories  
Compact Ball Valves (Regular Style)**



Socket/Threaded Style

Pressure Rating @ 73°F (23°C), Water  
 1/2" - 2" 235 psi  
 3" - 6" 150 psi  
 Flanged 150 psi  
 Maximum Service Temperature  
 CPVC = 200°F (93°C)  
 Temperature/Pressure De-ratings Apply  
 Rated for Vacuum Service

All Valves Assembled with Silicone-Free, Water Soluble Lubricants.  
 See Ball Valve Accessories & Repair Kits Section for Additional  
 Options & Features

Note: Standard 6" Valve uses Lever-Style Handle for proper leverage.  
 T-Handle option is more compact but will increase difficulty of  
 operation.

**CPVC**

Size	EPDM	Viton®	Std Pk	Mstr Pk	Disc Code
<b>Socket Ends</b>					
<b>1/2</b>	2122-005C <b>24.93</b>	2132-005C <b>27.72</b>	10	80	212
<b>3/4</b>	2122-007C <b>32.88</b>	2132-007C <b>36.96</b>	10	0	212
<b>1</b>	2122-010C <b>41.11</b>	2132-010C <b>46.21</b>	10	0	212
<b>1-1/4</b>	2122-012C <b>83.18</b>	2132-012C <b>92.39</b>	6	0	212
<b>1-1/2</b>	2122-015C <b>102.77</b>	2132-015C <b>108.04</b>	5	0	212
<b>2</b>	2122-020C <b>108.98</b>	2132-020C <b>122.45</b>	6	0	212
<b>3</b>	2122-030C <b>331.59</b>	2132-030C <b>369.84</b>	1	4	213
<b>4</b>	2122-040C <b>612.98</b>	2132-040C <b>688.69</b>	1	0	213
<b>6 (Lever Handle)</b>	2122-060C <b>1001.78</b>	2132-060C <b>1067.44</b>	1	0	213
<b>6 (Tee Handle)</b>	21226-060C <b>1001.78</b>	21326-060C <b>1067.44</b>	1	0	213

**Threaded Ends**

<b>1/2</b>	2121-005C <b>24.93</b>	2131-005C <b>27.72</b>	10	80	212
<b>3/4</b>	2121-007C <b>32.88</b>	2131-007C <b>36.96</b>	10	0	212
<b>1</b>	2121-010C <b>41.11</b>	2131-010C <b>46.21</b>	10	0	212
<b>1-1/4</b>	2121-012C <b>83.18</b>	2131-012C <b>92.39</b>	6	0	212
<b>1-1/2</b>	2121-015C <b>102.77</b>	2131-015C <b>108.04</b>	5	0	212
<b>2</b>	2121-020C <b>108.98</b>	2131-020C <b>122.45</b>	6	0	212
<b>3</b>	2121-030C <b>331.59</b>	2131-030C <b>369.84</b>	1	4	213
<b>4</b>	2121-040C <b>612.98</b>	2131-040C <b>688.69</b>	1	0	213

**Flanged Ends**

<b>1/2</b>	2123-005C <b>69.49</b>	2133-005C <b>72.30</b>	1	8	212
<b>3/4</b>	2123-007C <b>80.68</b>	2133-007C <b>84.76</b>	1	8	212
<b>1</b>	2123-010C <b>95.40</b>	2133-010C <b>100.52</b>	1	8	212
<b>1-1/4</b>	2123-012C <b>150.33</b>	2133-012C <b>159.56</b>	1	8	212
<b>1-1/2</b>	2123-015C <b>188.00</b>	2133-015C <b>193.81</b>	1	4	212
<b>2</b>	2123-020C <b>212.90</b>	2133-020C <b>226.37</b>	1	0	212
<b>3</b>	2123-030C <b>509.85</b>	2133-030C <b>548.10</b>	1	0	213
<b>4</b>	2123-040C <b>796.45</b>	2133-040C <b>872.15</b>	1	0	213
<b>6 (Lever Handle)</b>	2123-060C <b>1512.80</b>	2133-060C <b>1622.91</b>	1	0	213

**CPVC (continued)**

Size	EPDM	Viton®	Std Pk	Mstr Pk	Disc Code
<b>Flanged Ends</b>					
<b>6 (Tee Handle)</b>	21236-060C <b>1512.80</b>	21336-060C <b>1622.91</b>	1	0	213



## Thermoplastic Valves Compact Ball Valves (Regular Style) & Lab Ball Valves

### Compact Ball Valves (Regular Style)

#### CPVC (continued)

Size	EPDM	Viton®	Std Pk	Mstr Pk	Disc Code
<b>Flanged Ends</b>					
<b>2</b>	2123-020C <b>212.90</b>	2133-020C <b>226.37</b>	1	0	212
<b>3</b>	2123-030C <b>509.85</b>	---	1	0	213
<b>4</b>	2123-040C <b>796.45</b>	2133-040C <b>872.15</b>	1	0	213
<b>6 (Lever Handle)</b>	2123-060C <b>1512.80</b>	2133-060C <b>1622.91</b>	1	0	213
<b>6 (Tee Handle)</b>	21236-060C <b>1512.80</b>	21336-060C <b>1622.91</b>	1	0	213

### Lab Ball Valves



Socket/Threaded Valve Only

Pressure Rating @ 73°F (23°C), Water  
1/4" - 3/8" 150 psi  
Maximum Service Temperature  
PVC = 140°F (60°C)  
CPVC = 200°F (93°C)  
Temperature/Pressure De-ratings Apply  
Rated for Vacuum Service

All Valves Assembled with Silicone-Free, Water Soluble Lubricant

#### Valve & Adapters includes:

- 1 - Threaded 1/4" Valve
- 2 - O-ring Sealed 1/4" MPT x Mipt Adapters
- 2 - EPDM or Viton® O-rings (AS568-013 size)
- 1 - End Connector Wrench
- 2 - O-ring Sealed 1/4" MPT x 3/8" I.D. Tubing Barb Adapters
- OR -
- 2 - O-ring Sealed 1/4" MPT x 1/4" I.D. Tubing Barb Adapters



Valve & Adapters

#### PVC

Size	EPDM	Viton®	Std Pk	Mstr Pk	Disc Code
<b>Valve &amp; Adapters Threaded Ends</b>					
<b>1/4X1/4T</b>	1529-002A <b>24.46</b>	1539-002A <b>25.57</b>	1	25	218
<b>1/4X3/8T</b>	1529-002 <b>24.46</b>	1539-002 <b>25.57</b>	1	25	218

#### Valve only Threaded Ends

<b>1/4</b>	1521-002 <b>19.55</b>	1531-002 <b>21.76</b>	50	200	218
<b>3/8</b>	1521-003 <b>27.48</b>	1531-003 <b>30.47</b>	50	200	218

#### Valve only Socket Ends

<b>1/4</b>	1522-002 <b>19.55</b>	1532-002 <b>22.12</b>	50	200	218
<b>3/8</b>	1522-003 <b>27.48</b>	1532-003 <b>30.47</b>	50	200	218

#### CPVC

Size	EPDM	Viton®	Std Pk	Mstr Pk	Disc Code
<b>Valve &amp; Adapters Threaded Ends</b>					
<b>1/4X1/4T</b>	1529-002CA <b>29.36</b>	1539-002CA <b>29.93</b>	1	25	219
<b>1/4X3/8T</b>	1529-002C <b>29.36</b>	1539-002C <b>29.93</b>	1	25	219

#### Valve only Threaded Ends

<b>1/4</b>	1521-002C <b>23.51</b>	1531-002C <b>25.85</b>	50	200	219
<b>3/8</b>	1521-003C <b>32.97</b>	1531-003C <b>30.90</b>	50	200	219

#### Valve only Socket Ends

<b>1/4</b>	1522-002C <b>23.51</b>	1532-002C <b>27.98</b>	50	200	219
<b>3/8</b>	1522-003C <b>32.97</b>	1532-003C <b>36.60</b>	50	200	219